


U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
<b>SKINDICHT® BL-M ATEX</b>		14.11.2013

High degree of protection  
Cold impact resistance



Corrosion-resistant



Robust



Reliability



Temperature-resistant

### Application range

Equipment group II / Category 2G+1D  
Devices, machines and apparatus  
For mobile applications in offshore and marine industries  
Chemical and petrochemical industry

### Design

Metric connection thread acc. to EN 50262

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEx IBE 13.0029X
Material:	Body: nickel-plated brass O-ring: NBR
Protection rating:	IP 68
Temperature range:	-30°C to +90°C

Product Management	Document: LAPP_PRO1031EN.pdf	1 / 2
--------------------	------------------------------	-------



**SKINDICHT® BL-M ATEX**

14.11.2013

Part number	Article designation / size	SW (mm)	Thread length/ D (mm)	Outer Ø (mm)	PU
SKINDICHT® BL-M ATEX					
52103103	12 x 1,5	16	5.0	17,8	50
52103113	16 x 1,5	20	5.0	22.0	50
52103123	20 x 1,5	24	6.0	26,4	50
52103133	25 x 1,5	29	7.0	31,9	50
52103143	32 x 1,5	36	8.0	39,6	25
52103153	40 x 1,5	45	8.0	49,5	25
52103163	50 x 1,5	54	9.0	59.0	10
52103173	63 x 1,5	67	10.0	73,5	10