

# Specifications for BMP41/BMP51/BMP53 Labelmaker Tape

<b>Adhesive</b>	Permanent Acrylic
<b>Application</b>	Indoor & Outdoor Grade Facility & Safety Identification; Voice & Data Communication
<b>Article No.</b>	143375
<b>Brady Material No.</b>	<a href="#">B-595</a>
<b>Material Type</b>	Vinyl
<b>Colour</b>	Black on Yellow
<b>Finish</b>	Gloss
<b>Laboratory Application</b>	Well Plates; General Identification
<b>Description</b>	Durable, low-shrink vinyl with our most aggressive adhesive. Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper jacketed pipes, powder coated surfaces). Also adheres to difficult low energy surface items (PVC piping, blow-moulded equipment cases, ABS plastics, recycled plastics)
<b>Max. Service Temp. °C</b>	82
<b>Order Reference</b>	MC-500-595-YL-BK
<b>Printer Compatibility</b>	BMP41; BMP51; BMP53
<b>Shape</b>	Continuous
<b>Size - Length (m)</b>	7.62
<b>Size - Width (mm)</b>	12.70
<b>Additional Information</b>	Adhesive Stick on Strips, Cut to Size
<b>Total Qty per Pack</b>	1 Label(s) / Box
<b>Voice/Data Application</b>	Data Centre Equipment; Bay, Rack & Frame Labels
<b>Industry</b>	Data & Telecommunications; Facility & Safety Industry; Process
<b>Layout</b>	Continuous Roll
<b>Min. Application Temp. °C</b>	-18
<b>Min. Service Temp. °C</b>	-40
<b>Thickness (mm)</b>	0.1