

**PICCOLO PC B 85 G**



Sample photo

**Order symbol:** PC B 85 G  
**Product nbr:** 8724304  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074001979  
**EI. number:**  
 Finland: 3423403  
 Electric No. 8212001491  
 Denmark:  
 Electric No. Italy: 7201015  
 Electric No. Sweden: 2536804

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	110	80	85	B-3 FP 22040
inch:	4.3	3.1	3.3	DIN-35 Mounting rail Wall fastening lug (2 pcs)

Materials:	Rating:
<b>Material:</b> Polycarbonate	Ingress Protection (EN 60529): IP66/67
<b>Base colour:</b> RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
<b>Cover screws material:</b> Polyamide	Electrical insulation: Totally insulated
<b>Cover colour:</b> RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Cover screws colour:</b> Grey	UV resistance: UL 508
<b>Gasket material:</b> Polyurethane	Flammability Rating: UL 746C 5V
	Glow Wire Test (IEC 695-2-1) °C: 960
	NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13

Temperatures:	Certificates:
<b>Temperature °C (short term):</b> -40 ... 120 °C	Germanischer Lloyd (GL)
<b>Temperature °C (continuous):</b> -40 ... 80 °C	SGS Fimko
<b>Temperature °F (short term):</b> -40 ... 250 °F	Gost R
<b>Temperature °F (continuous):</b> -40 ... 175 °F	

Accessories:
B-MP                      Mounting plate

