






Abisolierlänge: 13mm
 stripping length: 13mm
 Anzugsmoment: 10mm² 16mm² 25mm²
 Tightning torque: 6Nm 6Nm 7Nm
 für Litze 10-25mm², AWG 6-4, feindrähtig
 for stranded wire 10-25mm², AWG 6-4, fine wire



 All Dimensions in mm Original Size DIN A 4			Techn. Character.				Nicht tolerierte Maße/Free size tolerances			
				Dat.	Name	Maßstab/Scale 2:1	100A Axialschraubkontakt, Stift 100A axial screw contact, male 10-25mm ² versilbert/silver plated			
			Detail.	21.02.11	gru					
			Insp.		Rü					
			Stand.							
			HARTING Electric GmbH & Co. KG					TB 09 11 000 6112		Blatt/ page /
A			D-32339 Espelkamp							
Mod.	Dat.	Name					Sub.			