






LOC	DIST	REVISIONS					
CE	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			2	ADD 2064938-4 AND 2-2064938-4	16MAR2010	BB	SM
			A	ECR-11-015831	06OCT2011	BB	SM

⚠ MATERIAL
PROTECTIVE COVER: TPE, COLOR: BLACK, UL94 HB*
FERRULE SUBASSEMBLY: ZIRCONIA/METAL
COMPRESSION SPRING: STAINLESS STEEL
FRONT HOUSING: PEI, COLOR: BEIGE, UL94 V-0*
INNER TUBING: PTFE, COLOR: CLEAR, UL VW-1
REAR BODY: METAL
BEND LIMITING BOOT: PP, COLOR: BEIGE, UL94 V-0*
BOOT AND SHORT BUFFER BOOT: TPE, COLOR: BEIGE, UL94 V-0*
CRIMP EYELET/HEAT SHRINK ASSY: ALUM. ALLOY,HEAT SHRINK:POLYOLEFIN,UL VW-1
DUPLEX CLIP: PP, COLOR: BEIGE, UL94 V-0*
3.0mm CRIMP EYELET: NICKEL PLATED BRASS
*RATED AT QUALIFYING THICKNESS.

2. INSTRUCTION SHEET: 408-8675 AVAILABLE FOR DOWNLOAD AT
www.tycoelectronics.com/documents OR
www.ampnetconnect.com/foguide.
3. BULK PACKAGE.



DUPLEX, 2.4mm JACKETED	2-2064938-4
DUPLEX, 3.0mm JACKETED	2-2064938-3
DUPLEX, 1.6-2.0mm JACKETED	2-2064938-2
DUPLEX, 900um BUFFERED	2-2064938-1
SIMPLEX, 2.4mm JACKETED	2064938-4
SIMPLEX, 3.0mm JACKETED	2064938-3
SIMPLEX, 1.6-2.0mm JACKETED	2064938-2
SIMPLEX, 900um BUFFERED	2064938-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.BRIGGS CHK S.MILLER APVD D.BAECHTLE	31MAR2009 31MAR2009 31MAR2009	TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME KIT, CONNECTOR, LC, MM, BULK PACK			
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		A200779	C-2064938	-	-
CUSTOMER DRAWING		SCALE 3:1		SHEET 1	OF 1	REV A	