

## Datasheet

# RS Pro M40 Black Nylon Cable Gland With Lock Nut, 22 to 32mm Cable Dia Range, IP68

RS Stock No: **669-4689**



## Product Details

RS Pro cable gland in black colour, has a thread size of M40. It has a cable diameter ranging from 22 to 32 mm. The cable made of plastic is IP68 rated. This nylon cable gland is supplied completely with lock nut and entry thread seal.

## Features and Benefits

- Manufactured from UL approved nylon 66
- Flammability rating to UL 94V-2
- Provides watertight seal to IP68
- Offers strain relief and protection for cables

**Specifications:**

Cable Diameter Range	22 to 32 mm
Colour	Black
IP Rating	IP68
Locknut Included	Yes
Material	Nylon 66
Maximum Cable Diameter	32 mm
Maximum Operating Temperature	+85°C
Minimum Cable Diameter	22 mm
Minimum Operating Temperature	-60°C
Operating Temperature Range	-60 to +150°C
Standards Met	UL 94V-2
Thread Size	M40