

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere. For environments where the right atmosphere needs to be created (e.g. bars and restaurants), the "DimTone" feature could be useful. This is a LED feature that creates a warmer tone once light is dimmed down to lower intensities.

Product data

• General Characteristics

Cap-Base	GU10
Bulb	- [-]
Rated Lifetime (hours)	40000 hr

• Light Technical Characteristics

Color Code	WW
Color Designation (text)	Warm White
Beam Angle	25 D
Beam Description	- [-]
Correlated Color Temperature	2700 K
Luminous Flux	300 Lm
Luminous Intensity	1200 cd
Color rendering index	90
Color Temperature	2700 K [CCT 2700K]
Rated Luminous Flux	300 Lm

• Electrical Characteristics

Wattage	8 W
Wattage Technical	8.0 W
Voltage	230 V
Line Frequency	50-60 Hz
Power Factor	0.9 -
Lamp Current mA	40 mA
Dimmable	Yes

Wattage Equivalent	50 W
Starting Time	0.5 (max) s

• Measuring Conditions

Switching cycle	50000x
-----------------	--------

• Product Dimensions

Diameter D	50 mm
Overall Length C	80 mm

• Product Data

Order code	929000213402
Full product code	929000213402
Full product name	MASTER LEDspotMV D 8-50W GU10 WW 25D Ra90
Order product name	MAS LEDspotMV D 8-50W GU10 WW 25D Ra90
Pieces per pack	1
Packing configuration	6
Packs per outerbox	6
Bar code on pack - EAN1	8718291192466
Bar code on outerbox - EAN3	8718291192473
Logistic code(s) - 12NC	929000213402
Net weight per piece	0.116 kg

