


## Datasheet

# 1.8m Male DB25 to Male C36 Parallel Cable Assembly

Stock Number: 182-4009



Connector A	Male DB25
Connector B	Male C36
Length	1.8m



**WIRE ASSIGNMENT :**

DB95 N.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	
DB95 W.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	
	Black	Brown	Red	Orange	Yellow	Green	Black	Purple	Grey	White	Pink	Light Green	Black/White	Brown/White	Red/White	Orange/White	Green/White	Blue/White	Purple/White	Red/Black	Green/Black	Yellow/Black	Green/Black	Grey/Black	Pink/Black	Shield	Shield	Shield	Shield	Shield	Shield	Shield	Shield	Shield	Shield	Shield	Shield

**Specifications**

Shielding	100% of Mylar Foil
Current Rating	2A max
Operating Voltage	300V max
Temperature Rating	60°C
Contact Resistance	15m ohm max
Mating Cycle	250