

Product Datasheet

Flexible PVC Hose, Green Tint



Applications: A multi-purpose hose for a medium duty suction and discharge use in the agricultural, industrial and aquatics market. Used in horticultural markets, turf management, in agricultural as seed drill hose, as injector hose and as an irrigation hose. Also suitable for slurries and dilute chemicals.

Advantages: Lightweight, flexible, transparent smooth bore. Easy to handle, extensive size range. Operates at low temperatures.

Specification:

RS Stock Number	Length m	I.D mm	Weight gr/mtr	Working Pressure bar	Bend Radius mm	Temp Range °C
8405466	10	19	275	8	75	-20 to +50°C
8405475	30	19	275	8	75	-20 to +50°C
8405478	50	19	275	8	75	-20 to +50°C
8405472	10	25	330	8	120	-20 to +50°C
8405481	30	25	330	8	120	-20 to +50°C
8405484	5	25	330	8	120	-20 to +50°C
8405488	10	32	460	7	150	-20 to +50°C
8405497	30	32	460	7	150	-20 to +50°C
8405490	5	32	460	7	150	-20 to +50°C
8405494	10	38	550	6.5	170	-20 to +50°C
8405504	30	38	550	6.5	170	-20 to +50°C
8405507	5	38	550	6.5	170	-20 to +50°C
8405501	5	50	810	6	220	-20 to +50°C
8405510	10	50	810	6	220	-20 to +50°C