

Datasheet

RS Pro Thermoplastic Knob, M8 x 12

RS Stock No: **702-7655**



Product Details

RS Pro thermoplastic knob in black colour, features M8 x 12 thread size, zinc plated steel, brass or stainless steel inserts. It is resistant to most chemicals, UV light and water absorption.

Features and Benefits

- Resistant to most chemicals, UV light and water absorption (1.5% maximum)
- Temperature range: -20 to +110°C (short term withstand +170°C)
- PP construction



ENGLISH

Specifications:

| | |
|-----------------------------|-----------------|
| Body Material | PP |
| Colour | Black |
| Insert Material | Stainless Steel |
| Knob Diameter | 40 mm |
| Knob Shape | Multiple Lobes |
| Mounting Type | Threaded Hole |
| Thread Diameter | M8 |
| Thread Length | 12 mm |
| Thread | M8 x 12 |
| Operating Temperature Range | -20 to +110°C |