



Sample photo

Order symbol: AL 122208
Product nbr: 7011230
Description: Enclosure
Remarks: Aluminium

EAN: 6418074004161
EI. number:
 Finland 3423619
 Denmark 8212004702
 Italy 7321055
 Sweden 2536321

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Rating:	
	L	W	H		
mm:	125	222	81	Ingress Protection (EN 60529): IP 66/67	
inch:	4.9	8.7	3.2	Impact Resistance (EN 50102): IK 08	
Materials:				NEMA Class: NEMA 1, 4, 4X, 12, 13	
Material:	AL			Certificates:	
Base colour:	RAL 7001			Underwriters Laboratories	
Cover colour:	RAL 7001			UL Canada	
Cover screws material:	Stainless steel				
Gasket material:	Polyurethane				
Temperatures:					
Short term:	-50 ... 140 °C				
Continuous:	-50 ... 80 °C				
Short term:	-60 ... 285 °F				
Continuous:	-60 ... 175 °F				
Accessories:					
AM 1212	Mounting plate				
AM 1222	Mounting plate				
ARH 12	DIN-35 Mounting rail				
ARH 22	DIN-35 Mounting rail				
MR 75005	Taptite screw				
MRS 28541	Wall fastening lug set				
PH A & AH A/B	Hinge set				

