

Name: **JONO luminaire**  
1x49W T5/G5 220-240V 0/50-60Hz, 1500mm  
Type: 796-1848



### Technical specification

Colour: RAL9010  
Material: Base aluminium (RAL9010) / diffuser opal polycarbonate  
Electronic control gear: x  
Enclosure class: IP44  
Length (mm): 1500 mm  
Light source: 1xT5 49W/G5  
Operating frequency (Hz): 0/50-60 Hz  
Rated power (W): 49W  
Rated voltage (V): 220-240 V  
Weight (kg): 1,870 kg  
Dimensions (mm) l x w x h: 1500x55x87 mm

