


**KEMET Part Number: EFG(01)-240X240T0800** **Not for New Design**  
 (UFSEFG010AT080, EFG(01)240X240T0800)

KEMET, EFG, Flex Suppressors, Noise Suppression



General Information	
<b>Series:</b>	EFG
<b>Style:</b>	Sheet
<b>Description:</b>	Flex Suppressor Halogen Free Type
<b>Features:</b>	High Frequency Specifications
<b>RoHS:</b>	Yes
<b>Qualifications:</b>	UL94 V-1
<b>Environment:</b>	Halogen Free, PVC Free, Lead Free
<b>Notes:</b>	Not recommended for new designs, please see EFG2(01)-240X240T0800 for replacement

Dimensions	
<b>Sheet Size</b>	240x240mm
<b>T</b>	0.1mm +/-0.05mm

Packaging Specifications	
<b>Tape Description:</b>	Without PET Tape (Txx00)
<b>Tape Thickness:</b>	0.03mm

Specifications	
<b>Temperature Range:</b>	-40/+105°C
<b>Magnetic Permeability:</b>	20 u At 3MHz
<b>Effective Frequency:</b>	10 GHz MAX
<b>Resistance:</b>	1 MOhms MIN
<b>Specific Gravity:</b>	3 Atm TYP
<b>Conductivity:</b>	0.22 W/m K
<b>Tensile Strength:</b>	3.5 MPa

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.