


## Crimp contact - SF-6CS2000 - 1605562

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.06 mm²...0.25 mm²



### Key commercial data

Packing unit	100 pc
Minimum order quantity	10 pc
GTIN	 4 046356 253611
Weight per Piece (excluding packing)	0.22 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### General

Contact type	turned
Contact diameter	1 mm
Contact type	Socket
Connection type	Crimp connection
Insertion/withdrawal cycles mechanical	50
Litz wire cross section min.	0.06 mm²
Litz wire cross section max.	0.25 mm²

### Classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701

# Crimp contact - SF-6CS2000 - 1605562

## Classifications

### eCl@ss

eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000796
ETIM 5.0	EC000796

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## Accessories

### Accessories

#### Crimping tool

Crimping pliers with digital display - SF-Z0025 - 1607452



Crimping pliers with digital display

## Drawings

Dimensioned drawing

Dimensional drawing