

AMP


WIRE RANGE

8 AWG

STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]



MS25036-118 CLASS 2	-	LOOSE PC	324045
MILITARY P/N AHN CLASS	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105° c		THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S.S. GOULDEN 6-18-93		 TE Connectivity									
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: -		DIMENSIONS: MM[INCHES]				TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD B. BARE 6-18-93		NAME TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 8 AWG							
	CIRCULAR MIL AREA: 6.64-10.5mm² [13,100-20,800] STRANDED		PRODUCT SPEC -																	
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111				MATERIAL COPPER PER ASTM B-152 NYLON (MIL-M-20693) TYPE 1 COLOR: RED		FINISH TIN PLATE PER MIL-T-10727		APPLICATION SPEC -		WEIGHT -		SIZE A3		CAGE CODE 00779		DRAWING NO C-324045		RESTRICTED TO -	
FOR ORDER ENTRY	1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.							CUSTOMER DRAWING				SCALE NTS		SHEET 1 of 1		REV D1		