


DRAWING MADE IN AMERICAN PROJECTION

LOC
G 14

©1956 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

LTR	DESCRIPTION	DATE	APPROVE
E	REDRAWN	3-25-70	FCY
F	REVISED	4-14-71	FCY
G	REV PER G-4732	7/22/88	2-2
H	REV/OG10-0094-98	2-3-99	ME/GT



TONGUE MATERIAL THK = .018 ±.002
FOR .050 TO .082 WIRE INSULATION DIA

WIRE TERMINAL	322001	BODY: COPPER (ASTM B 152) TIN PL (ASTM B 545) SLEEVE: COPPER (ASTM B 152) TIN PL (ASTM B 545) INSULATION: NYLON COLOR: YELLOW
QTY	DESCRIPTION	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS ±.005 ANGLES ±5°	CONTRACT NO. 11	AMP INCORPORATED HARRISBURG, PENNSYLVANIA
MATERIAL	DR. Jm E. 3-24-70 CHK. Jm E. 3-25-70 APPD. Swabel 3-26-70 REL. Jm E. 3-26-70 DSGN APPD. OTHER APPD.	NAME WIRE TERMINAL P/D G- SPADE WIRE SIZE: 26-22
SEE TABLE	SIZE A	CODE IDENT NO. 00779
		NUMBER 322001
	SCALE NTS	SHEET 1 OF 1