



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
E	B		B	EBD0-0189-04		22APR04	FWK

- NOTES:
- 1 SINGLE PACK IN ACCORDANCE WITH SPEC 107-3275
 - 2 100 TRAY PACK IN ACCORDANCE WITH SPEC 107-3275
 - 3 0.08μm Au PLATING OVER 1.27μm Ni PLATING
 - 4 0.76μm Au PLATING OVER 1.27μm Ni PLATING OVER 0.76μm Cu PLATING
 - 5 PASSIVATED
 - 6 FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
 - 7 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



RECOMMENDED
CABLE STRIPPING DIM'S



				1	1	-	-	STAINLESS STEEL	5	CAP	10
				-	-	1	1	STAINLESS STEEL	3	CAP	10
				1	1	-	-	STAINLESS STEEL	5	NUT	9
				-	-	1	1	STAINLESS STEEL	3	NUT	9
				1	1	-	-	STAINLESS STEEL	5	CLAMP	8
				-	-	1	1	STAINLESS STEEL	3	CLAMP	8
				1	1	-	-	STAINLESS STEEL	5	BODY	7
				-	-	1	1	STAINLESS STEEL	3	BODY	7
				1	1	1	1	BRASS	4	CENTER CONTACT	6
				1	1	1	1	STAINLESS STEEL		CIRCLIP	5
				1	1	-	-	STAINLESS STEEL	5	BODY	4
				-	-	1	1	STAINLESS STEEL	3	BODY	4
				1	1	1	1	SILICON		GASKET	3
				1	1	1	1	PTFE		INSULATOR	2
				1	1	-	-	STAINLESS STEEL	5	SHELL	1
				-	-	1	1	STAINLESS STEEL	3	SHELL	1
				2--1	2--0	1--1	1--0	MATERIAL		DESCRIPTION	ITEM
				2	1	2	1				
QUANTITY PER ASSY						PARTS LIST					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN
R.SMITH
04FEB04

CHK
S.PARLOW
04FEB04

APVD
F.WHEELER-KING
04FEB04

PRODUCT SPEC
108-3460

APPLICATION SPEC
411-3276

WEIGHT
-

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

NAME
SMA RIGHT ANGLE PLUG SOLDER, CLAMP
RG188A/U, 316/U, RG174A/U, URM95, KX38, KX22A
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1478912

RESTRICTED TO
-

SCALE
1:1

SHEET
1 OF 1

REV
B