



Datasheet

ENGLISH

Stock No: 219-178

RS Pro C 146 D Series 25 Way Male 10 → 15A Connector Kit, includes Gland, Hood, Insert



Image representative of range

Product Details

RS Heavy Duty Connector Kits

RS heavy duty connector kits are a practical solution for industrial applications

Zinc die cast alloy

Powder coating finish

Steel / zinc coated locking lever

Mechanical life: + 500 cycles

Temperature range: - 40°C to +100°C

Protection rating: IP65

Lever locking system

Conforms to DIN 43652

Contacts are ordered separately



ENGLISH

Specifications:

| | |
|--------------------|---------------------|
| Number of Contacts | 25 |
| Series | C 146 D |
| Current Rating | 10 → 15A |
| Gender | Male |
| Kit Type | Connector Kit |
| Thread Size | M25 |
| Voltage Rating | 250 V |
| Kit Contents | Gland, Hood, Insert |