

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

10-32-1051

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

5.08mm Pitch SPOX™ Wire-to-Board Header, Vertical, with Friction Lock, 5 Circuits

- Documents:
- 3D Model

Product Specification PS-5197-004 (PDF)
- Drawing (PDF)

Product Specification PS-5197-005 (PDF)
- Product Specification PS-5197-001 (PDF)

Product Specification PS-5281-002 (PDF)
- Product Specification PS-5197-003 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
TUV	R72090224
UL	E29179

General

Product Family	PCB Headers
Series	5281
Application	Power, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	SPOX™
UPC	800753611047

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1970.500/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.60mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	5.08mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5281Series

Mates With

5197 SPOX™ Crimp Terminal Housing

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	7A
Voltage - Maximum	250V
Material Info	
Old Part Number	5281-05A
Reference - Drawing Numbers	
Product Specification	PS-5197-001, PS-5197-003, PS-5197-004, PS-5197-005, PS-5281-002, RPS-5197-001, RPS-5281-001
Sales Drawing	SD-5281-001

This document was generated on 03/02/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION