

KEMET Part Number: MMK22.5225K250D15L4TRAY
(F601DM225K250C, MMK22,5225K250D15L4TRAY)

Capacitor, Film, Metallized Polyester, 2.2 uF, +/-10% Tol, -55/+100C, General Purpose, 250 VDC@85C, Lead Spacing=22.5 mm, Not For New Design, Please Check Possible Alternative Parts (AltPart)



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	26	MAX
H	18.5	MAX
T	9	MAX
S	22.5	+/-0.4
LL	5	NOM
F	0.8	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Tray
Package Quantity:	308

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polyester
Application:	General Purpose
Style:	Radial Box
Lead Form:	Wire Leads
Features:	Pulse
RoHS:	Yes

Specifications	
Capacitance:	2.2 uF
Voltage:	250 VDC
Tolerance:	+/-10%
Voltage AC:	160 VAC
Voltage:	193.8 VDC (100C)
Rated Temperature:	85C
Temperature Range:	-55/+100C
Dissipation Factor @ 1 kHz:	1%
Insulation Resistance:	4.55 GOhm
Inductance:	6
Maximum dVdT:	8 v/us
Miscellaneous:	Not For New Design, Please Check Possible Alternative Parts (AltPart)