

2		1					
LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E3	REV PER ECR 07-006476	20MAR07	JR	TM

AMP

WIRE SIZE




22-18 AWG
STRANDED

1. INSULATION DIA 3.43 [.135] MAX

2. FITS TAB 0.81 [.032] THK

3 EASIER INSERTION

4 PRELIMINARY - NOT FOR PRODUCTION



4000	PVC, BLACK	ON TAPE, REEL	4 2-184268-2
1000	PVC, BLACK	LOOSE PIECE	4 2-184268-1
3 4000	NYLON, RED	ON TAPE, REEL	4 1-184268-2
3 1000	NYLON, RED	LOOSE PIECE	4 1-184268-1
4000	NYLON, RED	TAPE MOUNTED	184268-2
1000	NYLON, RED	LOOSE PIECE	184268-1
QTY	SLEEVE MATL./COLOR	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA	29MAY96	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm		CHK M ELLIS	29MAY96	RECEPTACLE, 187 SERIES, LOW INSERTION FORCE, FASTON, PIDG, WIRE SIZE: 22-18 AWG			
		APVD B BARE	29MAY96				
		PRODUCT SPEC					
		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL BODY,BRASS .016		WEIGHT -		A3	00779	C-184268	-
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING			
		0 PLC ± -		SCALE	1:1	SHEET	1 OF 1
		1 PLC ± -					REV
		2 PLC ± 0.38 [.015]					E3
		3 PLC ± -					
		4 PLC ± -					
		ANGLES ± -					
		FINISH					
		BODY,TIN					