


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓	✓		D	REDRAWN-REVISED PER G-1479, G-1175, P85-0137 & P85-0138	2-13-86
✓	✓		E	OBSOLETE 1--4 PER G-2393	3-24-87
✓	✓		F	OBSOLETE 1--3 PER G-3358	4-22-88
✓	✓		G	REV PER G-4732	7-26-88
✓	✓		H	OBSOLETE 1--0 PER G-4184	1-16-88
✓	✓		J	OBS. 1--2 PER G-4216	3-30-89
✓	✓		K	REV/0720-0066-93	4-14-93



- 1 WIRE INSULATION DIA: SEE TABLE.
2 TONGUE MATERIAL THK.: .031 ± .002

	.115-.170	100	LOOSE PC, BOX	8-328281-1
OBSOLETE	.115-.170	100	ON TAPE, SM. BOX	1-328281-4
OBSOLETE	.115-.170	1000	ON TAPE, LG. BOX	1-328281-3
OBSOLETE	.105-.170	5000	ON TAPE, REEL	1-328281-2
	.115-.170	5000	ON TAPE, REEL	1-328281-1
OBSOLETE	.105-.170	5000	LOOSE PIECE	1-328281-0
	.115-.170	—	LOOSE PIECE	328281

	WIRE INS. DIA.	QUANTITY	DESCRIPTION	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .008 ANGLES ± —				
MATERIAL INSULATION: NYLON - BLUE BODY & SLEEVE: COPPER (CQ-C-576) FINISH BODY & SLEEVE: TIN PL (MIL-T-10727) .000100 MIN. THK.				
CONTRACT NO. DR UTA/RFB 10-4-85				
CHK P. M. T. / 10/12/12-13-86				
APPD C. M. T. / 10/12/12-13-86				
APPD				
DSGN APPD				
OTHER APPD				
AMP INCORPORATED Harrisburg, Pa.				
NAME TERMINAL P.I.D.G., SPADE WIRE SIZE: 16-14				
SIZE B FSCM NO 00779 DRAWING NO 328281				
SCALE NTS SHEET 1 OF 1				