



Dell 20 Monitor

Model E2014H
19.5" monitor

Reliable and efficient, offering essential features for home and business

The Dell 20 Monitor is your smart choice for unmatched reliability, essential productivity features, and energy-saving environment and regulatory compliance. In addition, the Dell 20 Monitor offers family entertainment features and the security of Dell's Limited Hardware Warranty¹ and Advanced Exchange Service².

The Dell 20 Monitor is perfect for:

- **Educational institutions (computer labs, classrooms)**
- **Call centers, data entry centers, sales order input and administration**
- **Task workers for basic office productivity**
- **Home use for Internet, shopping online**



Dell 20 Monitor | E2014H



Dell 20 Monitor | E2014H (19.5", 49.40 cm VIS)

The Dell 20 Monitor | E2014H (19.5", 49.40 cm VIS) offers you:

Essential features for business productivity and home entertainment

- Get awesome screen clarity when you view applications and spreadsheets on-screen with the HD resolution and fast 5 ms response time of the Dell 20 Monitor.
- Easily access peripherals and devices with the plug and play DVI-D and VGA ports.
- Adjust the monitor to your preferred angle with the smooth tilt function.

Reliability you can count on

- For business
 - Benefit from Dell's quality monitoring and rigorous product development stages which help ensure reliability, avoid downtime and keep your workforce productive.
 - Plan transitions easily with Dell's stable product life cycles and worldwide product availability.
- For home
 - Enjoy seamless compatibility with Dell monitors and Dell systems and accessories.
 - Experience reliability thanks to Dell's rigorous product testing and high quality standards.
- Enjoy peace of mind with Dell's Limited Hardware Warranty¹ and Advanced Exchange Service².

Environmentally conscious and energy efficient

- For business
 - Help reduce your business' carbon footprint and environmental impact with Dell monitors, which meet latest regulatory and environmental standards.
 - Help decrease energy costs with Dell monitors' increased energy efficiency.
- For home
 - Dell monitors' power efficiency can save you money.
- Manage power consumption wisely with PowerNap, a brightness dimming feature which, when enabled, puts the monitor into sleep mode when it's not in use.

Designed with essential features
for home and business



Connectors



Upgrade to P2014H⁵

Wide viewing angle, height-adjustable stand, 2 USB ports, DisplayPort 1.2, Premium Panel Guarantee**

Compare to E2013H

What's in the box?

Monitor, Stand, power cord, drivers, documentation media, Quick Set Up Guide and Safety Information, VGA cable, DVI-D cable.

Dell recommends that customers dispose used computer hardware, including monitors, in an environmentally sound manner. Potential methods include reuse of parts or whole products and recycling of product, components and/or materials. For more information, please visit http://dell.com/recycling_programs and www.dell.com/environment



Dell 20 Monitor | E2014H (19.5", 49.40 cm VIS)

Display

Model number	E2014H
Viewable image size (diagonal)	49.40 cm (19.45 inches)
Preset display area	~103576.32 sq-mm (~160.54 sq-inches)
Horizontal	432.0 mm +/- 1.32 mm (17.00 inches +/- 0.08 inches)
Vertical	239.76 mm +/- 3.42 mm (9.44 inches +/- 0.13 inches)
Maximum resolution	1600 x 900 at 60 Hz
Aspect ratio	16:9
Pixel pitch	0.27 (H) mm x 0.27 (V) mm
Brightness (typical)	250 cd/m ²
Color gamut (typical)	83% ³
Color depth	16.7 million colors
Contrast ratio (typical)	1000:1
Viewing angle (typical) (vertical/horizontal)	160°/ 170°
Response time (typical)	5ms (black to white)
Panel technology	TN (active matrix - TFT LCD), anti-glare
Backlight	LED

Connectivity

Connectors	VGA, DVI-D (HDCP)
Dell soundbar ⁴ (optional)	AC511
Remote asset management	Yes, via Dell Display Manager

Design features

Stand	Tilt only (Typical: 5° forward or 21° backward; Maximum: 5.5° forward or 22° backward)
VESA mounting support (wall mount kit sold separately)	100 mm x 100 mm
Security	Security lock slot and stand lock (security lock not included)

Power

AC input voltage/frequency/current	100 to 240 VAC/50 or 60 Hz ±3 Hz/1.5A (typical)
Power consumption (typical)	14 W
Power consumption standby/sleep mode	<0.5 W

Dimensions (with stand)

Height	358.8 mm (14.12 inches)
Width	473.9 mm (18.66 inches)
Depth	165.5 mm (6.52 inches)

Weight

Weight (panel only – no stand)	2.41 kg (5.31 lbs)
Weight (with stand)	3.14 kg (6.92 lbs)
Shipping weight	4.25 kg (9.37 lbs)

Standard service plan

- 3 years Advanced Exchange Service² & Limited Hardware Warranty¹

Environmental compliance

ENERGY STAR[®], TCO Certified Displays, EPEAT[®] Gold, China Energy Label, CEL, WEEE, ErP (EuP) Standards, Korea E-Standby

¹Registered in US and Canada only.

²In the event you discover even one bright pixel on our select range of monitors during the Limited Hardware Warranty¹ period, a free panel exchange is guaranteed.

³For a copy of the Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see dell.com/warranty.

⁴Advanced Exchange Service: Replacement part/unit dispatched, if needed, following completion of phone/online diagnosis. Fee charged for failure to return defective unit. Availability varies. Other conditions apply.

⁵Color gamut (typical) is based on CIE1976 (83 %) and CIE1931 (72 %) test standards.

⁶Launch date for sound bar varies across countries. Please check with your country sales representatives for more information.

⁷Please check with your sales representative for availability of upgrade product.

Based on Dell document Ad#G13000621 dell.com/monitors

Product availability varies by country. Please contact your Dell representative for more information.