



TOLERANCES: +/- 0.30 mm (+/- 0.012in)

宣又實	繪圖	DRA'D BY	日期	DATE	材質	MATE.	圖名TITLE:	圖號DWG NO:	版次REVISID:
		JACKY		2010/1/20		ALUMINIUM ALLOY ADC-12	HQ027		A

ITEM NO	DESCRIPTION
HQ027	NATURAL ALUMINIUM BOX<WITOUT THE GASKET>
HQ027S	@@ IP67 RATING @@<WITH THE SILICON GASKET>
HQ027EMS	@@ IP67 RATING @@<WITH THE SILICON & SHIELDED GASKET>

**MATERIAL:** ALUMINUM ALLOY #ADC-12

**FINISH:** NATURAL (NO SUFFIX)  
GRAY (SUFFIX -LG)  
BLACK (SUFFIX -BK)

- 1) SIX(6) M4 x 20mm (0.787") LG. SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE ±0.10mm TOLERANCE  
ALL OTHER DIMENSIONS HAVE ±0.30 mm TOLERANCE



宣又實

繪圖

DRA'D BY

JACKY

日期

DATE

2010/1/20

材質

MATE.

ALUMINIUM ALLOY ADC-12

圖名TITLE:

HQ027

圖號DWG NO:

版次REVISID:

A