


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION . 19
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓			E	REDRAWN-REVISED PER G-1478, G-1179, P85-0109 & P85-0110	11/21/53	<i>[Signature]</i>
✓			F	OBS REV G 2591	12/24/53	PMF
✓			G	REV PER G-4732	7/24/53	<i>[Signature]</i>
✓			H	OBSOLETE 2-3 PER G-3990	10/6/53	AG
✓			J	REV/0720-0060-93	4-2-55	TO/17/54



- 1. WIRE INSULATION DIA. - SEE TABLE
- 2. BODY FINISH: TIN PLATE (MIL-T-10727) .000100 MIN THK

WIRE INS DIA	QUANTITY	DESCRIPTION	PART NO
.115 - .170	100	LOOSE PC, BOX	8-320863-1
.115 - .170	100	ON TAPE, SM. BOX	2-320863-6
.115 - .170	1000	ON TAPE, LA. BOX	2-320863-7
.105 - .170	---	LOOSE PIECE	2-320863-2
.115 - .170	5000	ON TAPE, REEL	2-320863-2
.115 - .170	---	LOOSE PIECE	320863

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ±	CONTRACT NO DR UTA / RFB 9-30-53		AMP INCORPORATED Harrisburg, Pa.		
	CHK <i>[Signature]</i> 11-26-53				NAME WIRE TERMINAL P.I.D.G.-FLANGED SPADE WIRE SIZE: 16-14
	MATERIAL INSULATION: NYLON - BLUE BODY & SLEEVE: COPPER (33-C-576)		APPD <i>[Signature]</i> 11-26-53	SIZE B	FSCM NO 00779
	FINISH BODY: 2		APPD	DRAWING NO 320863	SHEET 1 OF 1
		DSGN APPD	SCALE NTS		
		OTHER APPD			