

Datasheet

RS Pro Insulated Crimp Spade Connector, 0.5mm² to 1.5mm², 22AWG to 16AWG, M6 Stud Size, Red Vinyl

RS Stock No: **613-9463**



Product Details

RS Pro insulated crimp spade connector in red vinyl colour, has 0.5 to 1.5 mm², 22 to 10 AWG wire size with M6 stud size. It is made from copper and tin plating. This spade terminal has vinyl insulation with flared design for easy wire insertion. The insulation of this electrical spade connector is colour coded to correspond with the wire size they are used with.

Features and Benefits

- Insulated crimp spade connectors made from copper with a tin plating
- Spade terminals is vinyl or nylon insulation with a flared design for easy wire insertion
- Insulation of these electrical spade connectors is colour coded to correspond with the wire size they are used with

**Specifications:**

Colour	Red
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Vinyl
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Overall Length	22 mm
Stud Size	M6.4
Thickness	0.75 mm
Width	9.5 mm
Wire Size	22 to 16 AWG
Current Rating	9 to 18 A
Temperature Rating	+105°C
Type	Butted Stem
Voltage Rating	600 V