

Metalclad

Plate Switches

- All plate switches are X-rated and can be used for switching inductive or fluorescent loads without de-rating
- Complete with surface mounting box
- Clear terminal markings
- Captive and backed out terminal screws
- Only one size 4mm screwdriver needed
- Terminals have large lead-ins
- In compliance with BS EN 60669-1
- 25-year guarantee

10 Amp

- M1203 1 gang 2-way
- M1204 2 gang 2-way
- M1205 3 gang 2-way



M1203



M1204



M1205

Data Plate & Modules

- Accepts standard 50x25mm modules
- 2-year guarantee for modules

Data Plate

- M1222 2 module

Modules

- S1428 Blank - 1/2 module - white
- S1429 Blank - 1 module - white
- S1430 Master telephone - white
- S1431 Secondary telephone - white
- S1432 RJ11 telephone - white
- S1433 CAT 5e - white
- S1434 CAT 6 - white
- S1435 Co-ax male - white
- S1436 Co-ax female "return" - white
- S1437 F type - white
- S1438 TV/FM DAB diplexer - white
- S1439 TV/FM DAB triplexer - white
- S1440 TV/FM DAB quadplexer - white
- S1441 HDMI - white
- S1447 16A 250V German socket
- S1448 15A 125V American socket
- S1449 16A 250V French socket



M1222



Back Boxes

all knockouts are 20mm diameter

	knockouts	
	sides	back
1g	5	1