



Save as PDF



2710 LED Headlight

EASY OPEN
BATTERY
HOUSING



- High-intensity LED main light
- Red and Green night vision lighting

The new 2710 features a high intensity LED main light with an optical 4x magnification allowing for a wide or penetrating beam. Additional features include: Low level red, green, or white light for preserving night vision, and a signaling red (S.O.S), and white beacon light.

- Click here for information on the [2720](#)



2710 LED Headlight ANSI FL1 Specifications

	High	
LIGHT SOURCE.	LED	
BATTERIES	2 AAA Alkaline (Included)	
CHARGE TIME		
VOLTAGE	3	
LENGTH	6.6 cm (2.58")	
WEIGHT W/ BATTERIES	0.09 kg (3 oz.)	
WEIGHT W/O BATTERIES	0.05 kg (1.9 oz.)	

Materials

Body	Lens	Shroud	Switch Type
ABS	PC		
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film

Configuration

Cat. #	Description
2710	2710 LED Headlight

2710 LED Headlight Accessories

No accessories are currently available for this product

**LIGHT
OUTPUT**

**RUNTIME
(hours/min)**

**BEAM
DISTANCE
(meters)**

**PEAK BEAM
INTENSITY
(candela)**

FL1 STANDARD	High	Low
	2h	
	34m	14 m.
	285cd	50cd