

Corrugated tube screw connection - WP-GR HF CTA M40 BK - 3241223


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Corrugated pipe adapter, with M40 internal thread, straight, black, IP66, for connecting corrugated pipes to HEAVYCON EVO plastic cable glands or ADVANCE plastic housings.



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 860857
Weight per Piece (excluding packing)	41.38 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP66

General

Color	black
Type	With strain relief
	Internal thread
Components	free from silicone, halogen, and cadmium
Inflammability class according to UL 94	V0
Material	PA
Assembly instructions	The corrugated pipe adapter is used in the screw connection instead of the union nut. Thanks to the adapter, corrugated pipes can be used.

Corrugated tube screw connection - WP-GR HF CTA M40 BK - 3241223

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27149109
eCl@ss 6.0	27140990
eCl@ss 7.0	27439204

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001469
ETIM 5.0	EC001469

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF-SL 42,5 BK - 3240848



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 10 m

Protective hose - WP-PA HF 42,5 BK - 3241089



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 25 m

Corrugated tube screw connection - WP-GR HF CTA M40 BK - 3241223

Accessories

Protective hose - WP-PA HF-HB 42,5 BK - 3240844



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 25 m

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>