

D

C

B



A

D





C

B

A



DETAIL Z



- CONTACTS DESIGNED FOR 28 AWG STRANDED OR 26,28, & 30 AWG SOLID WIRE.
- AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- STANDOFFS: POSN 8 (2) STANDOFFS AS SHOWN. POSN 14-18 (3) STANDOFFS, (1) CENTERED BETWEEN (2) SHOWN
- PLATED WITH .000100 - .000200 BRIGHT TIN LEAD OVER .000050 NICKEL.
- PLATED WITH .000030 GOLD OVER .000050 NICKEL.
- GOLD FLASH OVER .000050 NICKEL.
- HEIGHT AFTER TERMINATION IS .253 REF.
- INDICATES NO 1 POSITION.
- PLATED WITH .000005 MIN GOLD IN IDC AREA OVER .000050 MIN NICKEL.
- MOLDED PARTS: 94V-0 RATED THERMOPLASTIC, COLOR BLACK. CONTACTS: PHOS BRONZE.

	9	5	6	.900	9	1.088	.900	.950	19	20	1-746611-0	
	9	5	6	.800	8	.988	.800	.850	17	18		-9
	9	5	6	.600	6	.788	.600	.650	13	14		-8
	9	5	6	.300	3	.488	.300	.350	7	8		-7
	9	5	6	.700	7	.888	.700	.750	15	16		-6
OBSOLETE	4	5	6	.900	9	1.088	.900	.950	19	20		-5
OBSOLETE	4	5	6	.800	8	.988	.800	.850	17	18		-4
OBSOLETE	4	5	6	.700	7	.888	.700	.750	15	16		-3
OBSOLETE	4	5	6	.600	6	.788	.600	.650	13	14		-2
OBSOLETE	4	5	6	.300	3	.488	.300	.350	7	8	746611-1	
CONTACT FINISH				F	E	D	C	B	A	NO OF POSN	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL

11-29-04

L VARELA - DOCKS

CHK C. ROHDE

APVD M. WALMSLEY

PRODUCT SPEC

108-40013

APPLICATION SPEC

114-40005

WEIGHT

—

CUSTOMER DRAWING

11-29-04

NAME

KIT, AMP-LATCH DIP PLUG, PREASSEMBLED .100 X .300 CENTERS, 30 GOLD DUPLEX CONTACTS

SIZE

A1

CAGE CODE

00779

DRAWING NO

746611

RESTRICTED TO

—

Tyco Electronics Corporation

Harriaburg, PA 17105-3608

SCALE

10:1

SHEET

1

OF

1

REV

K