

Re-usable Nitrile 79-340

Technical Specifications

proFood™

Product description

Unsupported cotton flocked nitrile protective gloves.

Cuff finish : straight

Glove material

- copolymer of Butadiene-Acrylonitrile
- cotton flock

The glove is treated with Actifresh® - Sanitized®.

Characteristics

- Excellent physical properties
- Very good dexterity
- Silicon-free
- Use against following chemicals : Oils and greases ; Solvents ; Alcohols ; Aliphatic hydrocarbons ; Acids and Bases
- Tensile at break : 35 Mpa
- Elongation : 425 %
- Modulus 300 % : 11 Mpa
- Individually packed in pairs

Performance specifications

Abrasion resistance : Performance level 2
(> 500 - 2000 cycles)

Blade cut resistance : Performance level 0
(index 1.1)

Tear resistance : Performance level 0 (< 10 N)

Puncture resistance : Performance level 1
(average 30 N)

Liquidproof - Acceptable Quality level 0.65 or EN performance level 3

Chemical permeation : upon request

Gloves conform to the requirements of the European Directive 89/686/EEC and to the European standards EN 420, EN 388 and EN 374. They are categorised in "Complex Design" (= Protection against Mortal risks). EC-type examination certificate and EC Quality Control by:

*CENTEXBEL
Technologiepark 7
B-9052 Zwijnaarde*

Gloves conform to the requirements of the European Directive 89/109/EEC "Materials and Articles to Come into Contact with Foodstuffs", EC-type examination certificate received from:

*Laboratoire National d'Essais
5, Avenue Enrico fermi
F-78197 Trappes Cedex*

Migration against ethanol 10% : < 10 mg/dm²

Migration against acetic acid 3% : < 10 mg/dm²

Migration against iso-octane : < 20 mg/dm²

Application

Suitable for food contact : contact with aqueous foods, alcoholic foods, acidic foods and fatty foods with reduction factors 2 to 5.

Limitations of use

Do not use against fatty foods with reduction factor 1.

Do not use against flames or temperatures < -25 °C or > 100 °C.

Poor versus aromatic hydrocarbons, chlorinated solvents and many ketones.

Type	Finish	Reference	(EN) Sizes	Thickness	Length
Flocked	Lozenge	79-340	6 ^{1/2} - 7, 7 ^{1/2} -8, 8 ^{1/2} -9, 9 ^{1/2} -10	0.3 mm	300 mm

For more details (i.e. chemical protection), please contact :
Ansell Protective Products, Wijngaardveld 34 C, B-9300 Aalst
 Tel. : +32 - 53 71 05 05 Fax : +32 - 53 71 13 42