

CQD/NGG

Max-Flex, Flange Mounted, Variable Depth Operator



The Max-Flex™ flange mounted variable depth operator allows for the greatest degree of flexibility for operating the Siemens CQD and NGG compact enclosed molded case circuit breakers.

Due to the great ease of installation, the Siemens Max-Flex operator offers a substantial time and labor savings to the user when compared to other types of flange mounted operators.

The Max-Flex handle when mounted onto the enclosure flange, will accept up to three padlocks with a maximum shackle diameter of 3/8 inch.

max-flex

OPERATOR

SIEMENS

Enclosure Type	Application Length Inches	Complete Kit Catalog Number	Catalog Number Handle Only	Catalog Number Breaker Operator	Catalog Number Cable Only
1, 12, 3R	36	MFKG3R3			MFCF036
	48	MFKG3R4			MFCF048
	60	MFKG3R5			MFCF060
	72	MFKG3R6			MFCF072
	84	MFKG3R7	MFHM3R	MFMG	MFCF084
	96	MFKG3R8			MFCF096
	108	MFKG3R9			MFCF108
	120	MFKG3R10			MFCF120
	144	MFKG3R12			MFCF144

Enclosure Type	Application Length Inches	Complete Kit Catalog Number	Catalog Number Handle Only	Catalog Number Breaker Operator	Catalog Number Cable Only
4X	36	MFKG4X3			MFCF036
	48	MFKG4X4			MFCF048
	60	MFKG4X5			MFCF060
	72	MFKG4X6			MFCF072
	84	MFKG4X7	MFHM4X	MFMG	MFCF084
	96	MFKG4X8			MFCF096
	108	MFKG4X9			MFCF108
	120	MFKG4X10			MFCF120
	144	MFKG4X12			MFCF144