

Datasheet

30W LED Task Light



Description

This 30W LED task light is supplied with a 5m lead, and is ideal for use on site due to its durable die cast body. This task light is also cool to run and eliminates fire and burn hazards associated with halogen site lighting.

Features

- Daylight (6000K)
- 2100 lumens – replaces a 500W halogen
- Wide beam angle of 150°
- Complete with heavy duty steel floor stand
- 5m lead complete with 16A BS EN 60309 plug
- Cool running – no risk of fire
- IP65
- 110V
- Tripod stand available

Range

30W LED Task Light	7884616
Tripod Stand – 2m	7884625

Dimensions (mm)

	Height	Width	Depth
7884616	310	295	190

Technical Specification

Voltage	110V
Lamp Type	COB LED
Wattage	30W
Light Output	2100lm
Lamp Col. Temp	6000K
IP Rating	IP65
Body Material	Die Cast Aluminium
Frame Material	Steel

Standards

- BS EN 5098-1: 2008+A11: 2009
- BS EN 60598-2-5: 1999
- BS EN 61347-1: 2008
- BS EN 61347-2-13: 2006
- BS EN 55015: 2006+A2: 2009
- BS EN 61547: 2009
- BS EN 61000-3-2: 2006+A2: 2009
- BS EN 61000-3-3: 2008
- BS EN 60309: 1999