

Specifications for Vinyl tape for BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL

Adhesive	Permanent Acrylic
Article No.	142808
Brady Material No.	B-595
Material Type	Vinyl
Colour	White on Green
Finish	Gloss
Order Reference	M21-750-595-GN
Printable Area - Height (mm)	6400.00
Printable Area - Width (mm)	19.05
Printer Compatibility	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
Size - Length (m)	6.40
Size - Width (mm)	19.05
Additional Information	Average Outdoor Durability: 8 to 10 years
Thickness (mm)	0.1
Total Qty per Pack	1 Roll(s) / Box
Application	General & Industrial Identification; Laboratory Identification; Panel Identification
Continuous vs Die Cut Labels	Continuous Tape
Environment	Freezer
Industry	Laboratory;Electrical;Healthcare;BuildingsID
Laboratory Application	Well Plates;General Identification
Description	B-595 vinyl will adhere to difficult low surface energy items, including: PVC piping, blow-molded equipment cases, ABS plastics, powder-coated surfaces and equipment made from recycled plastics. The B-595 material also excels at sticking to highly textured surfaces such as painted cinder block walls, finished uneven wood, textured plastics, rough-pipes and paper-jacketed pipes.
Max. Service Temp. °C	82

