




Anschlussmaße nach EN 122340 / Mating face according to EN 122340 (a)



Innenleiter / inner conductor	CuZn39Pb3	Cu1Ni2Au1.27
Außenleiter / outer conductor	CuZn39Pb3	Cu1Ni2Au0.8
Schnapping / snap ring	CuBe2	Ni2Au0.8
Crimprohr / crimp ferrule	Cu SF w	Ni5Au0.2
sonstige Metallteile / other metal parts	CuZn39Pb3	Cu2Ni5Au0.2
Isolierung / insulator	PTFE	
 Kabel / cable	G 7: RG-174/U; RG-188A/U; RG-316/U; KX 3B; KX 22A	
 Montage / assembly	C3116	

M 1:1



a	14514	12.05.03	MA	97	Datum/date	Name/name	Werkstoff/ material
				gez./drawn	09.10.	ZM	
				gepr./appr.	09.10.97	BE	Oberfläche/ finish
				Norm/stand.			
Maßstab/scale				Benennung/title			
5:1 (1:1)				MMCX-Kabelwinkelstecker MMCX Angle Plug			
untol. Maße/ dim. without tolerances according to				Untert./doc.type	Zeichnungsnr./drawing no.		
				K	J01340A0051		
				Ersatz für/ replaces			
				 Telegärtner  Maße/dimensions: mm Original: DIN A4			