

HUBER+SUHNER® DATA SHEET

Within Series Adaptor: 32_MMBX-50-0-13/111_N



Description

Adaptor plug/plug
MMBX plug (male) / MMBX plug (male)
Slide - snap interface
Interface standard
Series MMBX - SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	12.4 GHz		
Frequency range	DC to 2.5 GHz	2.5 to 6 GHz	6 to 12.4 GHz
Return loss	≥ 32 dB	≥ 26 dB	≥ 15 dB

Mechanical Data

Number of matings	100
Weight	0.0004 kg

Environmental Data

Operating Temperature	-55 °C to 155 °C
2002/95/EC (RoHS)	compliant

Material Data

Piece Parts

Interface - MMBX plug (male)

	Material
Centre contact	Copper Beryllium Alloy
Outer contact	Bronze
Body	Bronze
Insulator	PFA / PTFE

Surface Plating

SUCOPRO Plating
SUCOPRO Plating
SUCOPRO Plating

Interface - MMBX plug (male)

Centre contact	Copper Beryllium Alloy
Outer contact	Bronze
Body	Bronze
Insulator	PFA / PTFE

SUCOPRO Plating
SUCOPRO Plating
SUCOPRO Plating

Related Documents

Outline drawing	DOU-00064707
-----------------	--------------

Ordering Information

Single package	32_MMBX-50-0-13/111_NE
Bulk 100 pcs package	32_MMBX-50-0-13/111_NH
Tray package	32_MMBX-50-0-13/111_NY

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions