



LOC	DIST	REVISIONS					
AG	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K2	REVISED PER ECO-11-018720	14SEP11	KBH	MM



DETAIL A
SCALE 10:1

SECTION B — B
SCALE 10:1

- 1 MATERIAL:
HOUSING: GLASS—FILLED POLYESTER, COLOR—SEE TABLE.
- 2 CONTACT PLATED WITH 0.00254 [.000100] TIN—LEAD OVER ALL.
- 3 CONTACT PLATED WITH 0.00038 [.000015] GOLD IN CONTACT AREA OVER 0.00127 [.000050] NICKEL OVER ALL.
- 4 PART NO. DENOTES INDIVIDUAL TWO POSITION SHUNT, WHICH IS PACKAGED ON BREAKAWAY COMBS OF TEN SHUNTS.
5. CONNECTOR MATES WITH WIRE WRAP POSTS, 0.64 [.025] SQUARE OR ROUND AND 0.56 [.022] X 0.66 [.026] POSTS. LENGTH 5.08 [.200] MINIMUM.
- 6 CONTACT PLATED WITH 0.00013 [.000005] GOLD IN CONTACT AREA OVER 0.00127 [.000050] NICKEL OVER ALL.
- 7 PART NO. DENOTES INDIVIDUAL TWO POSITION SHUNT WHICH IS PACKAGED LOOSE PIECE.
- 8 CONTACT PLATED WITH 0.00076 [.000030] GOLD IN CONTACT AREA OVER 0.00127 [.000050] NICKEL OVERALL.
- 9 CONTACT PLATED WITH 0.00254 [.000100] MATTE TIN OVER ALL.

		PHOSPHOR BRONZE	BLACK		2-382811-1	
			BLACK		2-382811-0	
			BLACK		1-382811-8	
			BLACK		1-382811-6	
OBSOLETE		BERYLLIUM COPPER	BLACK		1-382811-0	
			RED		382811-9	
			BLACK		382811-8	
			BLACK		382811-6	
			BLACK		382811-5	
D BY 382811-2		PHOSPHOR BRONZE	BLUE		382811-4	
			BLUE		382811-2	
OBSOLETE			BLUE		382811-1	
		CONTACT MATERIAL	HOUSING COLOR	FINISH	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W. SORAH 8-18-93		 TE Connectivity							
		CHK R. TALLEY 8-23-93									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ECONOMY SHUNT ASSEMBLY							
		APVD D. HUFFMAN 8-23-93									
0 PLC ± - 1 PLC ± - 2 PLC ± 0.26 [0.10] 3 PLC ± - 4 PLC ± - ANGLES ± ± -		PRODUCT SPEC 108-1476									
		APPLICATION SPEC 114-1059									
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
HOUSING CONTACT: SEE TABLE		 SEE TABLE		A2	00779	C-382811	-				
CUSTOMER DRAWING						SCALE	4:1	SHEET	1 of 1	REV	K2