







Panel cutting



Connector pitches on panel = 35 mm
Receptacle mating face acc. to
IEC 61076-3-106 - variant 04

jack references A and B
according to IEC 60603-7
the jack is located in the housing
in the X,Y,Z axis after locking clips.
- The assembled PC Board is delivered to customer
not locked in the housing.

Screwing by x4 M3 screws with torque 0.5 N.m
with flat washer under the screw .



				Dat.	Name	 All Dim. in mm Orig. Size DIN A 3	Push-pull RJ Industrial Easy install IP 67 receptacle and right angled jack 8 poles	Maßstab/ Scale 1,5:1
			Detail.	19/dec/05	JFB			
33812	23/oct/06	JFB	Insp.				TB 09 45 245 1130	Blatt/ Page 1 / 1
33468	10/may/06	JFB	Stand.					
33405	20/dec/05	BD						
33289	19/dec/05	BD						
Mod.	Dat.	Name	HARTING EURL F-95972 Paris				Sub.	