

BODY ZINC ALLOY
PLATED NICKEL

HOUSING PLOYESTER BUTYLENE TEREPHALATE
COLOR: BLACK

CENTER CONTACT PHOSPHOR BRONZE
PLATED GOLD


INSULATOR POLYPROPYLENE (94-V2)

MOUNTING POST BRASS
PLATED TIN






SOLDER TAIL BRASS WIRE
PLATED TIN

LOCKWASHER PHOSPHOR BRONZE
PLATED NICKEL



JAM NUT BRASS
PLATED NICKEL



RECOMMENDED MOUNTING HOLE
PANEL THICKNESS: 5.50(.217) MAX
RECOMMENDED MOUNTING TORQUE:
0.56 N (5 INCH-LBS) MAX



JAM NUT



LOCKWASHER

73171-6090	73100-0067 W/O NUT AND WASHER, PACKAGE BY TRAY
73171-2980	73100-0067, ONE PER BAG
73100-0067	PLASTIC TRAYS
PART NO.	PACKAGING

GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION
	mm	INCH	DRAWN BY DATE		BNC JACK, R/A, PCB RECEPTACLE, 75 OHMS BNC-J/RA/PCB			
4 PLACES	± ---	± ---	C.M.HUNG 1993/02/01					
3 PLACES	± ---	± ---	CHECKED BY DATE					
2 PLACES	± ---	± ---						
1 PLACE	± ---	± ---	APPROVED BY DATE		 MOLEX INCORPORATED			
ANGULAR ± 2 °		KWH 1993/04/01						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.			SHEET NO.
			SEE TABLE		SD-73100-0067			1 OF 1
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					