

## 3M™ Fuel™ X2 Premium Series

Glasses Fuel™ X2 have a special design with a smooth profile and rimless lenses on the bottom.

### Properties:

- Rubber, perfectly shaped, adjustable temples
- Polycarbonate lens with the absorption of 25 to 99.9% of UV radiation
- Design without bottom frames
- Tested according to EN166
- Soft, adjustable nose bridge
- Individually packed with bag microfiber, which, if necessary, protects and cleans the lens.
- Soft sides



**Product number** 7150600001

**Stock Number** DE272934667

**Colour of lens** Bronze lens

**Optical protection** UV protection unbiased perception of color

**Surface lens** Protection against scratches and fogging

**Filter Visor** 5-3.1.3M.1.FT

**Use**  
Building  
Forestry or horticulture  
Light Industry & Repairs

**Lens type** Polycarbonate visor

**Colour of frames** Brown

**Mechanical resistance** Low energy impact and impact at extreme temperatures (-5 / +55 ° C)

**Technical specifications** EN 166:2001

**Light transmission** 12%

**Features frames** 3M Fuel X2 EN166 FT CE 230.1