

# TradeMaster Tamper- Resistant Receptacle

885TRLA



Decorator Tamper-Resistant Receptacle.  
15 amp, 125 volt, Light Almond.

## features & benefits

- Meets 2008 National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet caps or protection plates.
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: Light Almond  
Type: Tamper-Resistant

**Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
cULus: Yes  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121704

**Dimensions**

Depth U S: 1"  
Height U S: 3.812"  
Width U S: 1.29"

**Technical Information**

Amps: 15 Amp

**Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: No