



IE FC RJ45 PLUG 180 2X2,
RJ45 PLUG CONNECTOR (10/100MBIT/S) WITH RUGGED
METAL HOUSING AND FC CONNECTING METHOD FOR
IE FC CABLE 2X2,
180 DGR CABLE OUTLET 1 PACK = 10 PCS

Transfer rate

- 1 / for Industrial Ethernet 10 Mbit/s
- 2 / for Industrial Ethernet 100 Mbit/s

Interfaces

Number of electrical connections

- for Industrial Ethernet FC TP cables 4
- for network components and terminal equipment 1

Design of the electrical connection / FastConnect Yes

Mechanical data

material / of the housing metal

Design, dimensions and weight

Width 13.7 mm

Height 16 mm

Depth 55 mm

Net weight 35 g

Permitted ambient conditions

Ambient temperature

- during operating -40 ... +70 °C
- during storage -40 ... +80 °C
- during transport -40 ... +80 °C

Relative humidity

<ul style="list-style-type: none"> • at 25 °C / without condensation / during operating / maximum 	95 %
Protection class IP	IP20
Product properties, functions, components / general	
Product feature / [not supplied - silicon-free]	Yes
Composant produit	
<ul style="list-style-type: none"> • décharge de traction 	Yes
Standards, specifications, approvals	
Verification of suitability	
<ul style="list-style-type: none"> • RoHS conformity 	Yes
<ul style="list-style-type: none"> • UL-registration 	Yes
letzte Änderung:	May 14, 2012