

Product Information

2477PJP125R05-28

EAN 4031582302158

Swivel castor with total lock, tail end of caster, Housing made of pressed steel, zinc-chromatised, double ball bearing swivel head, wheel axle with nut, Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, with threadguards, precision ball bearing

Wheel diameter	125 mm
Width of Tread	32 mm
Bolt-Ø	28 mm
Bolt lenght	45 mm
Offset	41 mm
Swivel Interference	262 mm
Overall height	163 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	1.141 Kg / daN
Dynamic Load capacity	100 Kg / daN
Static Load capacity	200 Kg / daN



Versions:

