


LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
		A3			REVISED PER ECO-11-005027	11MAR11	RK	HMR

D

C

B

A



- 1 STAMP AMP 8, APPROX AS SHOWN
- 2 MAX RECOMMENDED OPERATING TEMP. IS 170°C MAX
- 3 VOLTAGE RATING IS NOT APPLICABLE
- 4 WIRE CROSS SECTIONAL AREA RANGE: 13,100-20,800 CMA / 6.64-10.5mm2
- 5 COPPER PER ASTM B-152, ANNEALED
- 6 .000100 MIN TIN PLATE PER ASTM B-545


D

C

B

A

6	130550
FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 13FEB06		 TE Connectivity				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				
		CHK T MICHIELUTTI 13FEB06		TERMINAL, RING TONGUE, SOLISTRAND, WIRE SIZE: #8 —				
		APVD T MICHIELUTTI 13FEB06						
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL 		FINISH SEE TABLE		SIZE A3	CAGE CODE 00779	DRAWING NO C-130550	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 5:1	SHEET 1 OF 1	REV A3