




1/2" DR. E-TORX® SOCKET

PART NO.	SIZE	D1 MM	D2 MM	L MM			G.W. (kg)
13701	E10	13.0	22.0	38.0	6	72	5.0
13702	E12	15.0	22.0	38.0	6	72	5.3
13703	E14	17.0	22.0	38.0	6	72	5.9
13704	E16	19.0	22.0	38.0	6	72	6.7
13705	E18	21.0	23.8	38.0	6	72	5.5
13706	E20	23.5	25.8	38.0	4	48	4.4
13707	E22	25.8	25.8	38.0	4	48	5.2
13708	E24	27.8	27.8	40.0	4	48	6.2



⚠ These sockets should never be used on powers driver and / or extenders.

1/2" DR. QUICK-RELEASE RATCHET (TEAR DROP)

PART NO.	L MM			G.W. (kg)
13900	250	4	24	12.8



- Sata's ratchets feature a convenient single hand direction change switch.
- Sata's ratchets have quick-release capability to easily eject an engaged socket even under slippery conditions.

ANSI B107.10M
DIN 3122

1/2" DR. QUICK RELEASE RATCHET (ROUND HEAD)

PART NO.	L MM			G.W. (kg)
13901	250	4	24	14.8



- Sata's ratchets have quick-release capability to easily eject an engaged socket even under slippery conditions.

ANSI B107.10M
DIN 3122

1/2" DR. QUICK RELEASE RATCHET (TEAR DROP)

PART NO.	L MM			G.W. (kg)
13902	250	4	24	14.8



- Sata's ratchets feature a convenient single hand direction change switch.
- Sata's ratchets have quick-release capability to easily eject an engaged socket even under slippery conditions.

ANSI B107.10M
DIN 3122

1/2" DR. QUICK-RELEASE STUBBY RATCHET

New

PART NO.	L MM			G.W. (kg)
13960	140	6	24	10.4



- Sata's ratchets feature a convenient single hand direction change switch.
- Sata's ratchets have quick-release capability to easily eject an engaged socket even under slippery conditions.

ANSI B107.10M
DIN 3122

1/2" DR. HEAVY DUTY OFFSET QUICK-RELEASE RATCHET

New



PART NO.	L MM			G.W. (kg)
13970	261	4	20	13.6



- Sata's ratchets feature a convenient single hand direction change switch.
- Sata's ratchets have quick-release capability to easily eject an engaged socket even under slippery conditions.

ANSI B107.10M
DIN 3122

1/2" DR. WOBBLE EXTENSION BAR


PART NO.	L INCH	A MM			G.W. (kg)
13904	5"	12.7	4	24	6.2
13905	10"	12.7	4	24	12.9





- For wobble Function.
- Push in for Standard Extension Bar.

ANSI B107.10M
DIN 3123

⚠ These sockets accessories should never be used on powers driver and / or extenders.



1/2" DR. LOCKING EXTENSION BAR

PART NO.	L INCH	A MM			G.W. (kg)
13906	3"	12.7	4	120	26.7
13907	5"	12.7	4	24	6.6
13908	10"	12.7	4	24	12.9



- No more dropped sockets, extensions or universal joints, One hand on and quick release off.

ANSI B107.10M
DIN 3123

⚠ These sockets accessories should never be used on powers driver and / or extenders.

