

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		E1	REV PER ECR 09-027840	23DEC09	JR	TM

D


C

B

A



STYLE A



STYLE B
INSULATION RESTRICTING

- 1 STAMP "AMP - SEE TABLE" APPROX AS SHOWN
- 2 WIRE INSULATION DIA: SEE TABLE
- 3 TONGUE MATERIAL THK: .040±.002
- 4 BODY: TIN PLATE .000100 MIN EXT THK PER ASTM B545
- 5 SLEEVE: TIN PLATE .000100 MIN EXT THK PER ASTM B545
- 6 SLEEVE: NICKEL PLATE PER QQ-N-290
- 7 BODY & SLEEVE- CU PER ASTM B152
INSULATION - NYLON PER ASTM D4066
COLOR - YELLOW
- 8 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 9 MEETS MS25036-158, CLASS 2
- 10 MEETS M7928/1-62, CLASS 2
- 11 MEETS M7928/1-69, CLASS 2

D

C

B

A

500	LOOSE PIECE	10	.119-.200	10	BROWN	B				52077-2						
500	LOOSE PIECE	12	.095-.200	12	YELLOW	B				52077-1						
500	LOOSE PIECE	12-10	.150-.230	12-10	---	A				52077						
QTY	PACKAGE TYPE	STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY	SLEEVE	PART NO							
							FINISH									
RATING	THIS DRAWING IS A CONTROLLED DOCUMENT.						Tyco Electronics Corporation Harrisburg, PA 17105-3608 TERMINAL, RING TONGUE, PIDG WIRE SIZE: 12-10 AWG									
	DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN	23DEC09						NAME				
					CHK	23DEC09										
			0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± -		T MICHIELUTTI								SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
					APVD											
T MICHIELUTTI																
MATERIAL		FINISH		PRODUCT SPEC												
				APPLICATION SPEC												
				WEIGHT		-										
				CUSTOMER DRAWING		SCALE		5:1	SHEET	1 of 1	REV	E1				