

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [10-11-2033](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 254 Crimp Housing, High Pressure, 3 Circuits](#)

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-7879 \(PDF\)](#)
[Packaging Specification PK-7880-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [7880](#)
Application Signal, Wire-to-Board
Overview [KK® Interconnect System - Molex](#)
Product Name KK® 254
UPC 800753612280

Physical

Circuits (maximum) 3
Color - Resin Natural (White)
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Material - Resin Nylon
Net Weight 0.294/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Stackable No
Temperature Range - Operating See Product Specification

Material Info

Old Part Number 7880-3B

Reference - Drawing Numbers

[Packaging Specification](#) PK-7880-001
[Product Specification](#) PS-7879
[Sales Drawing](#) SD-7880



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[7880Series](#)

Mates With
[KK®254 PCB Headers 42375](#) , [42377](#) ,
[42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With
[7879](#) KK® High Pressure Crimp Terminal