

Datasheet

RS Pro Non-Fused Terminal Block, 12 Way/Pole, Screw Terminals, 22 to 12 AWG Free Hanging, Panel Mount, PA
RS Stock No: **763-8122**



Product Details

Rs Pro non-fused terminal block in black, has polyamide housing and M3.5 steel nickel plated screws. This block with 12 ways, features screw termination. This terminal block with 22 to 12 AWG wire, supports free hanging and panel mounting types. The terminal block with 750 V voltage rating, has brass contact with tin plating.

Features and Benefits

- 0.8 Nm maximum torque
- Operating temperature of -40 to +105°C
- 9.5 mm pitch
- 15 A current rating

Specifications:

Contact Material	Brass
Contact Plating	Tin
Current Rating	15 A
Material	Polyamide Housing
Maximum Operating Temperature	+105°C
Minimum Operating Temperature	-40°C
Mounting Type	Free Hanging, Panel Mount
Number of Ways	12
Pitch	9.5 mm
Termination Method	Screw
Voltage Rating	750 V
Wire Size	22 to 12 AWG
Colour	Black
Dimensions	131 x 18.5 x 13 mm
Screw Size	M3.5
Standards Met	RoHS, CE (BS EN 6.998)