



TOLERANCES: +/- 0.30 mm (+/- 0.012in)

宣又實

繪圖

DRA'D BY

日期

DATE

材質

MATE.

圖名TITLE:

圖號DWG NO:

版次REVISID:

JACKY

2010/1/20

ALUMINIUM ALLOY ADC-12

HQ033

A

ITEM NO	DESCRIPTION
HQ033	NATURAL ALUMINIUM BOX(WITOUT THE GASKET)
HQ033S	@@ IP67 RATING @@(WITH THE SILICON GASKET)
HQ033EMS	@@ IP67 RATING @@(WITH THE SILICON & SHIELDED GASKET)

MATERIAL: ALUMINUM ALLOY #ADC-12

FINISH: NATURAL (NO SUFFIX)
 GRAY (SUFFIX -LG)
 BLACK (SUFFIX -BK)

- 1) EIGHT(8) M4 x 20mm (0.787") LG. SCREWS
 SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE ±0.10mm TOLERANCE
 ALL OTHER DIMENSIONS HAVE ±0.30 mm TOLERANCE



宣又實

繪圖

DRA'D BY

JACKY

日期

DATE

2010/1/20

材質

MATE.

ALUMINIUM ALLOY ADC-12

圖名TITLE:

HQ033

圖號DWG NO:

版次REVISID:

A