

# DIN rail, unperforated - NS 32 CU/35QMM UNPERF 2000MM - 1201358


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



G-profile DIN rail, material: Copper, unperforated, height 15 mm, width 32 mm, length 2 m



## Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 017262
Weight per Piece (excluding packing)	1640.0 g
Custom tariff number	74072190
Country of origin	Germany

## Technical data

### Dimensions

Height	15 mm
Length	2000 mm
Width	32 mm

### General

Material	Copper
Coating	uncoated
Color	copper-colored
Test standard	Acc. to EN 60715

## Classifications

### eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143

# DIN rail, unperforated - NS 32 CU/35QMM UNPERF 2000MM - 1201358

## Classifications

### eCl@ss

eCl@ss 5.1	27141143
eCl@ss 6.0	27400602

### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

## Drawings

